



Datasheet

Stock No: 324-8384

ENGLISH

# RS Pro Fahrenheit/Centigrade Dial Dry Thermometer Suitable For Various Applications



## Product Details

### Centre Back and Vertical 100mm Diameter Immersion Thermometers

Bi-metal element thermometers with applications in the heating and ventilation process, and refrigeration industries

- Dual scale
- Acrylic Window
- Temperature range covers both hot & chilled water applications
- Manufactured to DIN 16203
- 1/2 in. BSP Brass Male Thread
- Vertical entry types: 324-8384, 324-8413, 324-8407, 324-8429

## Specifications:

Thermometer Type:	Dial
Suitable Applications:	Heating & Ventilation, Refrigeration Industry
Temperature Scale:	Both
Filling Type:	Dry
Case Material:	Steel
Case Diameter:	100mm
Maximum Temperature Sensed:	+60°C
Minimum Temperature Sensed:	-20°C
Temperature Sensitive Range:	-20 → +60°C