




Timing Pulleys HTD5M-15

5mm pitch for 15mm wide belt
Centre drilled or Pilot Bore

in Steel or Aluminium with Zinc plated Steel Flanges

ENGLISH



Mat'l	Code	No. Teeth	Type	Dp	De	Df	Dm	F	L	Bore	No. Flanges
st.	P12-5M-15F	12	1F	19.10	17.96	23	13	20.5	26	-	2
st.	P14-5M-15F	14	1F	22.28	21.14	25	13	20.5	26	6	2
st.	P15-5M-15F	15	1F	23.87	22.73	28	16	20.5	26	6	2
st.	P16-5M-15F	16	1F	25.46	24.32	28	16.5	20.5	26	6	2
st.	P18-5M-15F	18	1F	28.65	27.51	32	20	20.5	26	6	2
st.	P20-5M-15F	20	1F	31.83	30.69	36	23	20.5	26	6	2
st.	P22-5M-15F	22	1F	35.01	33.87	39	25.5	20.5	26	6	2
st.	P24-5M-15F	24	1F	38.20	37.06	42	27	20.5	28	6	2
st.	P26-5M-15F	26	1F	41.38	40.24	44	30	20.5	28	6	2
st.	P28-5M-15F	28	1F	44.56	43.42	48	30.5	20.5	28	6	2
st.	P30-5M-15F	30	1F	47.75	46.60	51	35	20.5	28	6	2
st.	P32-5M-15F	32	1F	50.93	49.79	54	38	20.5	28	8	2
st.	P36-5M-15F	36	1F	57.30	56.16	60	38	20.5	28	8	2
st.	P40-5M-15F	40	1F	63.66	62.52	71	38	20.5	28	8	2
Alu.	P44-5M-15	44	3	70.03	68.89	-	38	20.5	30	8	-
Alu.	P48-5M-15	48	3	76.39	75.25	-	38	20.5	30	8	-
Alu.	P60-5M-15	60	3	95.49	94.35	-	50	20.5	30	8	-
Alu.	P72-5M-15	72	3	114.59	113.45	-	50	20.5	30	8	-