

AT-FS716L

Unmanaged Fast Ethernet Switches



AT-FS716L-xx

16 port 10/100TX unmanaged 'Green' switch with internal power supply

ECO-Friendly

The AT-FS716L eco friendly switch conforms with Allied Telesis' commitment to environmentally friendly processes and products. It is designed to minimize power consumption through the use of a high efficiency power supply and a low power chipset.

With a low 2.8W typical power consumption*, and a reduction in power during after-work hours (overnight mode) – as well as other power saving features included as standard, the Allied Telesis AT-FS716L truly lives up to its name as an 'eco friendly' switch.

Not only does this help the planet by reducing the carbon footprint of each switch, it also lowers the Total Cost of Ownership (TCO) to the user, as the product costs less to run, and has improved reliability.

With all of these power saving features, the new eco friendly AT-FS716L saves the user up to 48% in power consumption over our previous version (see power saving table).

High Performance

Providing powerful 10/100 switching solutions for desktop and small network environments, the Allied Telesis FS700 series of unmanaged switches features full auto-negotiating 10/100 ports. These ports enable the switches to detect the speed and duplex modes of attached devices, enabling them to automatically configure for the best possible performance.

Flexibility

Available as 5, 8, 16, or 24 port models, the FS700 series meets a multitude of power requirements with both internal and external power-supply options. Also, wall, desk, and rack-mounting options give users ultimate flexibility in selecting the model that meets their physical deployment requirements.

Simplified Installation

Fully auto-configuring FS700 series switches require minimal set-up by the user. Auto-sensing ports enable seamless and simple connectivity between existing 10Mbps Ethernet and 100Mbps Fast Ethernet UTP devices—and all units can be installed in minutes. Every FS700 series model is equipped with MDI/MDI-X ports for simple connection to other hubs and switches. Finally, easy to read front panel LEDs show ongoing switch status and simplify troubleshooting.

Quality and Reliability

Allied Telesis is a worldwide leader in unmanaged Ethernet switches. Shipping more than 250,000 unmanaged switches each year, Allied Telesis offers proven reliability and industry recognized quality.

Key Features

- 16 10/100TX ports
- Wirespeed technology
- Non-blocking architecture
- Auto-negotiation ports
- Auto MDI/MDI-X ports
- Transparent to VLAN packets
- Half and full-duplex flow control
- Sturdy metal case
- Rack-mountable

Power-saving Features

- Maximum switch power consumption
LED push button OFF : 5.17W @ 100Mbps
LED push button ON : 4.67W @ 100Mbps
- Typical switch power consumption* - 2.8W
- Overnight mode - when PCs are powered off, the switch reduces power
- Power down mode
- Measure and minimize - checks the lengths of the cable and sends only enough power for specific cable length



* 9 ports connected with 3m cables.

AT-FS716L | Unmanaged Fast Ethernet Switches

Performance

14,800pps for 10Mbps Ethernet
148,000pps for 100Mbps Fast Ethernet

Throughput 2.38Mpps
Switching capacity 3.2Gbps

MAC addresses Up to 8K

Packet buffer 160K

Half/full-duplex
Auto negotiation
Auto MDI/MDI-X on all ports

Interface Connections

10/100TX RJ-45

Power Characteristics

Frequency 50 to 60Hz
12V/0.3A

Environmental Specifications

Operating temp. 0°C to 40°C (32°F to 104°F)
Non-operating temp. -25°C to 70°C (-13°F to 158°F)
Operating humidity 5% to 80% non-condensing
Storage humidity 5% to 95% non-condensing

Technical Specifications

Physical Characteristics

Dimensions 18.4cm x 12.4cm x 4.4cm
(7.24" x 4.88" x 1.73")
Weight 0.8kgs (1.76lbs)

Wall-mount or Desktop

All units come with wall and 19" rack-mount brackets

Standards and Compliance

IEEE 802.3 10T Ethernet
IEEE 802.3u 100TX Fast Ethernet
IEEE 802.3x Flow control

Electrical/Mechanical Approvals

UL 1950
CSA 22.2 No. 950
FCC/EN55022 Class B
VCCI Class B
EN60950 (TUV)
EN55024
CE

LED Indicators

Indication	Quantity	Color	Status
System Power	1	Green	Green : Power ON OFF : Power OFF
LINK/ACTIVITY	1	Green/ Orange	Orange : 100M link up Green : 100M link up OFF : Link down Flashing : Data transmitting
FDX/HDX	1	Green	Green : The port is operating in full-duplex mode Flashing : When collision is present OFF : The port is operating in half-duplex mode
Push button	(for port LED only)		OFF : Normal port LED status ON : Port LED power saving mode. Turn off all port LED. Only power LED on.

AT-FS716L | Unmanaged Fast Ethernet Switches

Power Saving % Chart

Ports	Status	Non-green vs Green Power Saving %	
		3m cable	100m cable
		AC side	AC side
Overnight mode		61.1%	58.7%
16 port	Only link, no traffic	43.3%	40.5%
	Smartbit, 100% utilization TX	43.1%	40.1%
15 port	Only link, no traffic	43.9%	41.1%
	Smartbit, 100% utilization TX	44.2%	41.4%
14 port	Only link, no traffic	44.5%	41.7%
	Smartbit, 100% utilization TX	44.8%	41.9%
13 port	Only link, no traffic	45.1%	42.2%
	Smartbit, 100% utilization TX	44.6%	41.8%
12 port	Only link, no traffic	45.8%	42.8%
	Smartbit, 100% utilization TX	45.3%	42.5%
11 port	Only link, no traffic	46.4%	43.4%
	Smartbit, 100% utilization TX	46.7%	43.7%
10 port	Only link, no traffic	47.0%	44.0%
	Smartbit, 100% utilization TX	46.8%	43.2%
9 port	Only link, no traffic	47.7%	44.6%
	Smartbit, 100% utilization TX	48.0%	44.9%
8 port	Only link, no traffic	48.4%	45.5%
	Smartbit, 100% utilization TX	48.2%	45.1%
7 port	Only link, no traffic	49.1%	46.1%
	Smartbit, 100% utilization TX	49.4%	46.4%
6 port	Only link, no traffic	49.7%	46.7%
	Smartbit, 100% utilization TX	49.7%	46.8%
5 port	Only link, no traffic	50.4%	47.4%
	Smartbit, 100% utilization TX	50.8%	47.7%
4 port	Only link, no traffic	51.1%	48.0%
	Smartbit, 100% utilization TX	51.3%	48.4%
3 port	Only link, no traffic	51.8%	48.7%
	Smartbit, 100% utilization TX	51.2%	48.5%
2 port	Only link, no traffic	52.5%	49.4%
	Smartbit, 100% utilization TX	52.9%	49.7%

Ordering Information

AT-FS716L-xx

16 port 10/100TX unmanaged switch with internal power supply

Where xx = 10 for U.S. power cord
 20 for no power cord
 30 for U.K. power cord
 40 for Australian power cord
 50 for European power cord

USA Headquarters | 19800 North Creek Parkway | Suite 100 | Bothell | WA 98011 | USA | T: +1 800 424 4284 | F: +1 425 481 3895

European Headquarters | Via Motta 24 | 6830 Chiasso | Switzerland | T: +41 91 69769.00 | F: +41 91 69769.11

Asia-Pacific Headquarters | 11 Tai Seng Link | Singapore | 534182 | T: +65 6383 3832 | F: +65 6383 3830

www.alliedtelesis.com

© 2010 Allied Telesis Inc. All rights reserved. Information in this document is subject to change without notice. All company names, logos, and product designs that are trademarks or registered trademarks are the property of their respective owners. 617-000352. Rev. B