

Socket - EM-DUO 120/20/GFI - 5602519

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Key commercial data

Packing unit	1
GTIN	 4 046356 688406
Custom tariff number	85366990

Technical data

Dimensions

Width	83 mm
Height	134 mm
Depth	49 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

General

Nominal voltage U_N	125 V AC
Nominal current I_N	20 A
For country-specific use in	USA
	Canada
	China
	Japan
	Mexico
	Peru
	Saudi Arabia
	Taiwan
	Thailand
	Phillipines
	Venezuela
	Vietnam

Socket - EM-DUO 120/20/GFI - 5602519

Technical data

General

Color	ivory
Insulating material	PVC 94 V0
Standards/regulations	UL 508
	CSA 22.2

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	30
Conductor cross section AWG/kcmil max	10
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3

Classifications

eCl@ss

eCl@ss 4.0	27142305
eCl@ss 4.1	27142305
eCl@ss 5.0	27143412
eCl@ss 5.1	27130801
eCl@ss 6.0	27130803
eCl@ss 7.0	27130803
eCl@ss 8.0	27130803

ETIM

ETIM 3.0	EC001325
ETIM 4.0	EC001663
ETIM 5.0	EC001663

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620