

HUBER+SUHNER® DATA SHEET

Coaxial PCB Connector: 82_MBX-50-0-3/111_N

Rev.: E 

Description

Straight PCB jack

Interface Standards
HUBER+SUHNER MBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type through holes
Weight 0.000725 kg

Environmental Data

Operating Temperature -55 °C to 155 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Brass
Outer contact	Brass
Body	Brass
Insulator	LCP (Liquid crystal polymer)

Surface Plating

SUCOPRO Plating
SUCOPRO Plating
SUCOPRO Plating

Related Documents

Outline drawing	DOU-00144733
Catalogue drawing	DCA-00161423
Mounting hole	DPA-00144881

Ordering Information

Tape and Reel package	82_MBX-50-0-3/111_NM
Bulk 100 pcs package	82_MBX-50-0-3/111_NH
Single package	82_MBX-50-0-3/111_NE

Remarks

PCB connector with stand-offs

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions