



ENGLISH

Datasheet

**RS Pro Thermal Interface Sheet, Graphite, Silicone,
5W/m-K, 150 x 150mm 0.6mm**

RS Stock No: **707-4812**



Product Details

RS Pro thermal interface sheet measures 150 x 150 mm and has graphite, silicone construction. This stable, easy-to-assemble sheet has a thermal conductivity of 5 W/m.K. It is suitable for operating temperatures ranging from -40 to +200°C.

Features and Benefits

- Good heat spreader
- Good thermal conductivity
- Easy to assemble
- High stability

**Specifications:**

Colour	Grey
Dimensions	150 x 150 mm
Length	150 mm
Material	Graphite, Silicone
Maximum Operating Temperature	+200°C
Minimum Operating Temperature	-40°C
Operating Temperature Range	-40 to +200°C
Thermal Conductivity	5 W/mK
Thickness	0.6 mm
Width	150 mm
Standards Met	REACH, RoHS