

## PAD25M3ABS - Break Stem Open

| General Part Information    |                   |                                                                                   |
|-----------------------------|-------------------|-----------------------------------------------------------------------------------|
| Product Description         |                   | PAD25M3ABS                                                                        |
| Article Number              |                   | 62999.00                                                                          |
| Rivet Type                  | <a href="#">i</a> | Break Stem Open                                                                   |
| Standard Bulk Pack Quantity |                   | 1000.00                                                                           |
| Application / Features      | <a href="#">i</a> |  |

| Geometry / Dimensions / Performance |                   |        |
|-------------------------------------|-------------------|--------|
| Head Style                          | <a href="#">i</a> | Domed  |
| Body Diameter Ø (mm)                |                   | 2.40   |
| Body Length (mm)                    |                   | 7.30   |
| Min. Grip Range (mm)                |                   | 3.20   |
| Max. Grip Range (mm)                |                   | 4.80   |
| Min. Hole Diameter (mm)             |                   | 2.60   |
| Max. Hole Diameter (mm)             |                   | 2.60   |
| Min. Flange Diameter (mm)           |                   | 4.10   |
| Max. Flange Diameter (mm)           |                   | 4.40   |
| Flange Thickness (mm)               |                   | 0.71   |
| Mandrel Diameter (mm)               |                   | 1.50   |
| Nominal Shear Strength (N)          |                   | 270.00 |
| Nominal Tensile Strength (N)        |                   | 330.00 |

| Material / Finish / Weight |                   |           |
|----------------------------|-------------------|-----------|
| Body Material              | <a href="#">i</a> | AlMg99.5  |
| Mandrel Material           |                   | Aluminium |
| Finish                     |                   | Clean     |
| Weight per thousand (kg)   |                   | 0.40      |

