
PARATHOM CLASSIC B 40 6 W/827 E14 FR

PARATHOM CLASSIC B | LED lamps, classic mini-candle shape, with retrofit screw base



Areas of application

- General illumination
- Domestic applications
- Chandeliers
- Outdoor use in outdoor luminaires only (minimum IP65)

Product benefits

- Very low energy consumption
- Extremely long life
- Robust against vibrations
- No UV and near-IR radiation in the light beam
- Instant 100 % light, no warm-up time
- Simple direct replacement for conventional incandescent lamps
- Lower thermal output (compared with the standard reference product)

Product features

- Professional LED lamps for line voltage
- Not suitable for use with dimmers
- Base: E14
- Mercury-free lamps
- Good quality of light; color rendering index $R_a \geq 80$; constant chromaticity



Technical data

Electrical data

Rated wattage	6.00 W
Nominal wattage	6.00 W
Nominal voltage	220...240 V
Operating frequency	50...60 Hz
Power factor λ	0.52
Claimed equiv. conventional lamp power	40 W


Photometrical data

Nominal luminous flux	470 lm
Rated luminous flux	470 lm
Color temperature	2700 K
Color rendering index Ra	80
Lumen main.fact.at end of nom.life time	0.70
Light color as per EN 12464-1	Warm White
Standard deviation of color matching	≤ 6 sdc _m
Lumen maintenance at end of service life	0.70

Light technical data

Warm-up time (60 %)	0.00 s
Starting time	< 0.5 s

Dimensions & weight



Overall length	110.0 mm
Diameter	38.0 mm
Outer bulb	B40
Length	110.0 mm

Product datasheet

Lifespan

Nominal lamp life time	20000 h
Rated lamp life time	20000 h
Number of switching cycles	100000

Additional product data

Base (standard designation)	E14
Mercury-free	Yes
Appropriate disposal acc. to WEEE	Yes
Footnote only for product	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value/In development, data preliminary

Capabilities

Dimmable	No
----------	----

Certificates & standards


Energy efficiency class	A+
Energy consumption	6 kWh/1000h

Country specific categorizations

ILCOS	DRBB/F-5,8-220-240-E14-38/110
Order reference	PARCLB40 6W/827

Light Distribution

Product datasheet



Spectral power distribution



Guarantee

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4052899912144	PARATHOM CLASSIC B 40 6 W/827 E14 FR	Shipping carton box 10	127 mm x 88 mm x 210 mm	2.35 dm ³	756.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

Product datasheet

For further products and actual information concerning LED lamps see

▶ www.osram.com/ledlamps

For Guarantee see

▶ www.osram.com/guarantee

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.