



ENGLISH

Datasheet

Stock No: 534-913

**RS Pro Closed End Wire Splice**

**Connector, Clear, Insulated, Tin Plated**

**2.5 → 6 mm<sup>2</sup>**



## Product Details

### RS Pro Closed End Wire Splices

Closed end wire splices with tin plated copper sleeves and transparent nylon 6.6 insulation. These closed end wire splices are ideal for electrically joining cables or for storing/insulating the ends of spare cables, which may be required at a later date. Choose the correct crimp by adding all conductor cross-sectional areas together (mm<sup>2</sup>). For suitable crimp tool for these closed end wire splices please see stock no. 253-4583.



ENGLISH

## Specifications:

Splice Type	Closed End
Wire Size	2.5 → 6 mm <sup>2</sup>
Overall Length	24.1mm
Diameter	10.5mm
Insulation	Insulated
Colour	Clear
Insulation Material	Nylon
Contact Material	Copper
Contact Plating	Tin