





LOC —	DIST —	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
			A	REVISED PER ECO-09-014471	18JUN09	HMR	CR	


MATERIALS AND FINISH:
HOUSING: PA 6-6, UL94V-0, COLOR: GREEN.
CLAMP: BRASS, NICKEL PLATED.
CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M2, BRASS, NICKEL PLATED.

ELECTRICAL:
VOLTAGE RATING: 300V
CURRENT RATING: 11A
WIRE SIZE RANGE: 14-30 AWG

ENVIRONMENTAL:
OPERATING TEMP RANGE: -40°C TO +110°C



56.0	16	1-1986371-6
52.5	15	1-1986371-5
49.0	14	1-1986371-4
45.5	13	1-1986371-3
42.0	12	1-1986371-2
38.5	11	1-1986371-1
35.0	10	1-1986371-0
31.5	9	1986371-9
28.0	8	1986371-8
24.5	7	1986371-7
21.0	6	1986371-6
17.5	5	1986371-5
14.0	4	1986371-4
10.5	3	1986371-3
7.0	2	1986371-2
DIM L	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 18MAR2008	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm		CHK C RICHARD 3/19/08				
		APVD C RICHARD 3/19/08	NAME TERMINAL BLOCK, PLUG, VERTICAL STACKING LEFT HAND, 3.50mm PITCH			
		PRODUCT SPEC				
		APPLICATION SPEC	SIZE A3			
MATERIAL —		WEIGHT —				
		FINISH —	CAGE CODE 00779			
			DRAWING NO C-1986371			
		CUSTOMER DRAWING			RESTRICTED TO —	
		SCALE NTS			SHEET 1 OF 1	REV A