

EK EKH 180 T-3FSH



Sample photo

Order symbol: EKH 180 T-3FSH
Product nbr: 9996228
Description: Enclosure, PC
Remarks: Transparent hinged cover

EAN: 6418074053398
EI. number:
Finland: 3435908
Electric No. Sweden: 9996228

Including: Flanged Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	560	380	180	EKH	Base, PC
inch:	22.0	15.0	7.1	EKUN	Base, PC
Materials:				EKU 30-G	Cover
Material:	Polycarbonate			EKU 30-T	Cover
Base colour:	RAL 7035 -light grey			EKUVT	Mounting plate
Cover screws material:	Polyamide			EKUXT	Mounting plate Pertinax
Cover colour:	Clear transparent			EKV 32	DIN-35 Mounting rail
Cover screws colour:	Grey			EKUZR	Extension frame
Gasket material:	Polyurethane			Rating:	
Temperatures:				Ingress Protection (EN 60529): IP65	
Temperature °C (short term):	-40 ... 120 °C			Impact Resistance (EN 62262): IK08	
Temperature °C (continuous):	-40 ... 80 °C			Electrical insulation: Totally insulated	
Temperature °F (short term):	-40 ... 250 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (continuous):	-40 ... 175 °F			UV resistance: UL 508	
Accessories:				Flammability Rating: UL 746C 5V	
EKUM	Base, PC			Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
Accessories:				Certificates:	
				Gost R	

