

General Information

Extended Product Type:	JSBRT11 24DC
Product ID:	2TLA010025R0000
EAN:	7350024432732
Catalog Description:	JSBRT11 24DC Safety relay
Long Description:	Safety relay with many outputs. Power supply 24VDC. Relay outputs 7NO/2NC

Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Safety Relays
 Products » Low Voltage Products and Systems » Control Products » Safety Products » Safety Relays

Ordering

EAN:	7350024432732
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85364110

Dimensions

Product Net Width:	0.100 m
Product Net Height:	0.072 m
Product Net Depth:	0.118 m
Product Net Weight:	0.610 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	0.127 m
Package Level 1 Height:	0.080 m
Package Level 1 Length:	0.105 m
Package Level 1 Gross Weight:	0.605 kg

Safety Information

Safety Category Acc. to ISO 13849-1: 4

Additional Information

Product Main Type:	JSB
Product Name:	Safety Relay
Rated Control Supply Voltage (U _s):	24 V DC
Suitable For:	Interlocking switch/Gate/Hatch, Light curtains, Light beams, Emergency stop, Hold to run/Enabling device, Foot control device, Area supervision, Output expansion

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	2TLC172001C0202_chapter06
Declaration of Conformity - CE:	2TLC172078D0201

Classifications

E-nummer:	3861113
ETIM 4.0:	EC001449 - Device for monitoring of safety-related circuits
ETIM 5.0:	EC001449 - Device for monitoring of safety-related circuits
Object Classification Code:	K

