

## General Information

Extended Product Type:	263RS6
Product ID:	2CMA167476R1000
EAN:	7392696674768
Catalog Description:	Surface socket-outlet, 6h, 63A, IP44, 2P+E
Long Description:	Surface socket-outlet, earthing sleeve position 6h, rated current 63A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Blue

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Surface Socket Outlets

## Ordering

EAN:	7392696674768
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

## Dimensions

Product Net Width:	107 mm
Product Net Height:	254 mm
Product Net Length:	136 mm
Product Net Depth:	254 mm
Product Net Weight:	0.95 kg

## Container Information

Package Level 1 Width:	116 mm
Package Level 1 Length:	267 mm
Package Level 1 Height:	145 mm
Package Level 1 Gross Weight:	0.95 kg
Package Level 1 EAN:	7392696674768
Package Level 1 Units:	1 piece

## Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

## Additional Information

Additional Information:	Cable entry, M32, alternative rear knock-out cable entry
Cable Cross-Section:	6 ... 25 mm <sup>2</sup>
Color:	Blue
Degree of Protection:	acc. to IEC 60529 IP44
Enclosure Material:	Thermoplastic polyester (PBT)
Frequency (f):	50 Hz 60 Hz
Function:	Surface socket outlet
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#263RS6
Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	RS
Product Name:	Industrial Socket Outlet
Protection Type:	Splashproof
Rated Current (I <sub>n</sub> ):	63 A
Rated Voltage (U <sub>r</sub> ):	200 ... 250 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2
Suitable For:	Surface Socket Outlets

Suitable for Product Class: Industrial Plugs and Sockets

### Classifications

E-nummer: 2416508

UNSPSC: 39120000

