

A great-looking everyday carry torch equipped with the latest multi-function technology for unprecedented personal light management. It showcases the attributes of Smart Light Technology (SLT), pioneered specially by LED Lenser in response to calls for selective light settings for different situations. SLT includes three light modes – Professional, Easy, Defence - and up to 8 different light settings: Power, Low Power, Dim, Blink, Boost, SOS, Defence and Morse. Needless to say the M7 has them all so that precisely the right light option can be chosen for any given task. Additionally, two energy usage modes also help set the torch to optimise either run-time or lumen output. These settings are interchangeable in milliseconds from a single Dynamic Switch on the end of the barrel. This light is flawless, bright and even because of its class-leading LED and the Advanced Focus System, an in-built patented application which makes the transition from flood to spot beam seamless and homogenous. Thanks to a specially-calibrated internal reflector lens this light spreads evenly across the widest possible area whilst ensuring pinpoint accuracy for telescopic illumination too - in this case as far as 280 metres at a maximum 400 lumens. There's also a single hand sliding Speed Focus with a fast-lock mechanism at the lamp head, a strong but elegant casing made from aircraft-grade aluminium, a helpful Low Battery Message System and gold-plated contacts for efficient energy transmission. Supplied with 4 x AAA batteries, wrist strap and belt pouch.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability second to none.

- Multi-function, medium sized torch packed with dazzling technology
- Energy efficient CREE Power+ LED Light Chip
- Increased light output from wide-angle, calibrated reflector lens
- State-of-the-art, reliable German engineering
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Smart Light Technology™. Micro-chip controlled multi-option technology with two energy usage modes, three pre-set light programs utilising eight light options (Morse, Dim, Boost, Power, Low Power, Blink, SOS, Defence Strobe)
- Dynamic Switch™ - Reactive, single switch control
- Speed Focus™ enables smooth single-handed beam focusing
- Fast Lock™ - locks the beam position and prevents accidental refocusing.
- Low Battery indicator
- Robust, yet lightweight aircraft-grade aluminium housing
- User-friendly modular design
- Corrosion resistant gold plated contacts for better conductivity
- Water and dust resistant (IPX54)

Technical Information

Size: 132 x 37mm Ø

Power: 400 lumens max

Run Time: up to 30 hours

Beam Distance: up to 280m

Weight: 190grams

Supplied with : Wrist-strap, belt/storage pouch and Duracell® Batteries (4xAAA)

Code	Colour	Packaging	Barcode
8307	Black	Gift Box	4029113830706