

Terminal strip marker carrier - KLM-A - 1004348


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Terminal strip markers, for strip marking, adjustable height, for use with end clamps E/UK, E/NS 35 N or CLIPFIX 35, lettering field size: 44 x 7 mm

The illustration shows a combination of versions KLM-A, and ESL 44 x 7

Key commercial data

Packing unit	1 PCE
Minimum order quantity	100 PCE
Catalog page	Page 347 (CL2-2011)
GTIN	 4 017918 012038
Custom tariff number	39269097
Country of origin	GERMANY

Technical data

General

Length (b)	46 mm
Width (a)	9.5 mm
Color	transparent
Inflammability class according to UL 94	HB
Ambient temperature (operation)	-40 °C ... 80 °C
Components	free from silicone and halogen
Material	ABS

Classifications

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761

Terminal strip marker carrier - KLM-A - 1004348

Classifications

ETIM

ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410
UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

Accessories

Accessories

Marking

Insert strip - ESL 44X 7 - 0808244

Insert strip, Sheet, white, Unlabeled, Can be labeled with: Office-Drucksysteme, Plotter, Perforated, Mounting type: Insert, Lettering field: 44 x 7 mm



Insert label - EMT (44X7)R - 0819275



Insert label, Roll, white, Unlabeled, Can be labeled with: Thermomark R, Thermomark X, Thermomark S, Mounting type: Insert, Cable diameter: 16-35 mm, Lettering field: 44 x 7 mm

