

Specifications for BMP71 Label Printer Labels

Adhesive	Permanent Acrylic
Article No.	114810
Brady Material No.	B-499
Material Type	Nylon Cloth
Colour	White
Finish	Matt
Order Reference	M71-30-499
Printer Compatibility	BMP71
Size - Height (mm)	19.05
Size - Width (mm)	38.10
Additional Information	Low profile;High adhesion
Thickness (mm)	0.166
Total Qty per Pack	250 Label(s) / Box
Vertical Repeat (mm)	22.23
Wire Gauge	0
Approval/Compliance	UL Recognised;CSA Accepted;Halogen Free (DIN VDE 0472/part 815)
Ribbon Series	M71-R4300
Application	Laboratory Identification; Rating & Nameplate Labels; Wire & Cable Marking
Environment	Freezer; Liquid Nitrogen; Autoclave
Industry	Data/Telecommunications;Electrical;Facility & Safety Identification;General Industry;Healthcare;Laboratory;Manufacturing;Process
Laboratory Application	Bottles, Flasks & Dishes;Conical & Large Tubes;Petri Dishes;Well Plates
Description	Labels for the BMP™71 Label Printer. Please Note: This material is UL approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use.
Max. Characters per Line	18
Max. Lines of	16

Text	
Max. Service Temp. °C	90
Max. Wire/Cable Diameter (mm)	9.10
Min. Service Temp. °C	-40
Shape	Rectangle
Surface	For smooth, textured/rough or Highly textured/Low surface energy surfaces
Vial/Tube (ml)	50.0 ml