

Cable sleeve - CES-SRC-BK - 0801718

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Small, unslotted cable sleeves suitable for cables with a diameter of 2 ... 11 mm, material: NBR




Product description

Unslotted sleeves for accommodating cables and lines with a diameter of 2 ... 11 mm, can be used in CES sealing frames



Key commercial data

Packing unit	10 pc
GTIN	 4 046356 675185
Weight per Piece (excluding packing)	9.03 g
Custom tariff number	40169300
Country of origin	Taiwan

Technical data

Dimensions

External cable diameter	2 mm ... 11 mm
-------------------------	----------------

Ambient conditions

Degree of protection	IP54 (DIN IEC 60529)
	IP65 (when using a CES-B..SFFS-PLBK sealing frame with screw locking directly on the housing panel (perpendicular mounting or underwall mounting) and a 3.6 mm wide cable binder (e.g., item 3240744))
Ambient temperature (operation)	-40 °C ... 125 °C (static)

General

Product description	Unslotted sleeves for accommodating cables and lines with a diameter of 2 ... 11 mm, can be used in CES sealing frames
Material	NBR
Color	black

Cable sleeve - CES-SRC-BK - 0801718

Classifications

eCl@ss

eCl@ss 4.0	27081002
eCl@ss 4.1	27081002
eCl@ss 5.0	27081002
eCl@ss 5.1	27081002
eCl@ss 6.0	27081002
eCl@ss 7.0	27081002
eCl@ss 8.0	27081002

ETIM

ETIM 3.0	EC000879
ETIM 4.0	EC000451
ETIM 5.0	EC000451

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Accessories

Accessories

Cable tie

Cable tie - WT-HF 2,5X98 BK - 3240733




Cable binders for quick and secure bundling, standard version

Drawings

Cable sleeve - CES-SRC-BK - 0801718

Dimensioned drawing



Dimensional drawing