



Cable glands Progress nickel-plated brass with antikink nozzle EPDM

One-piece sealing insert
Not overall length insulated

Material: Nickel-plated brass

Seal: NBR

O-ring: NBR

antikink nozzle: EPDM

minimal operation temperature: -40°C

maximum operation temperature: +100°C

Protection class: IP 68

Further protection: IP 69K



Ref	Thread	Ø clamping mini	Ø clamping maxi	Wrench size	H	T	Thread length L
A1008.52	M8x1.25	3.8	4.8	11	12	25	6
A1007.52	Pg 7	4.0	6.0	16	20	35	6
A1009.52	Pg 9	6.0	8.8	20	24	45	6
A1011.52	Pg 11	6.0	8.8	20	24	45	6
A1013.52	Pg 13	10.5	13.0	24	28	73	6

