

General Information

Extended Product Type:	CPM
Product ID:	1SNA187312R1400
EAN:	3472591873122
Catalog Description:	CPM Protecting Covers
Long Description:	- CPM cover protects the user from accidental touch on live circuits, - It is clipped onto the end sections (FE), onto the intermediate sections (FJ) and onto the SCF, SCFT or SCFM separators, - It can also be used for marking the terminal unit by means of a blank strip RTC, which slides into the cover.

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C
Color:	Transparent
Country of Origin:	Poland (PL)
Customs Tariff Number:	39269097
Declaration of Conformity - CE:	1SND225001C1009
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
E-number:	2925650
EAN:	3472591873122
Function:	Protecting Covers
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Insulation Material:	Polyamide
Invoice Description:	CPM Protecting Covers
Minimum Order Quantity:	10 piece
Mounting Type:	CPM cover protects the user from accidental touch on live circuits. It is clipped onto the end sections (FE), onto the intermediate sections (FJ) and onto the SCF, SCFT or SCFM separators. It can also be used for marking the terminal unit by means of a blank strip RTC, which slides into the cover.
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Object Classification Code:	X
Order Multiple:	10 piece
Package Level 1 EAN:	3472591873122
Package Level 1 Gross Weight:	0.25 kg
Package Level 1 Units:	10 piece
Package Level 2 Units:	850 piece
Package Level 3 Units:	13600 piece
Product Main Type:	CPM
Product Name:	Cover
Product Net Depth:	5.3 mm
Product Net Height:	30 mm
Product Net Weight:	25 g
Product Net Width:	500 mm
Selling Unit of Measure:	piece
Suitable For:	HD10/12.F5

HD10/12.FF5
HD120/30.F10
HD185/36.F12
HD35/16.F6
HD4/10.F4.19
HD4/9.F4
HD6/14
HD6/22.F12G
HD6/30.F12G
HD70/22.F8
M10/10
M16/12
M16/12.2A.G
M35/16
M35/16.2A.2G
M4/6
M4/6.NC
M6/8
M6/8.NC
MA2.5/5
SCF

