

Datasheet


FLUSH-MOUNTING SOCKET 6P+E IP66/IP67






TechData

| | |
|----------------------------|-----------------------|
| Rated current | 32A |
| Commercial series | OPTIMA-SEVEN Series |
| Poles | 6P+E |
| Hour position | 6h |
| Rated voltage | 380-415V |
| Working frequency | 50Hz |
| Working frequency | 60Hz |
| Colour | RED |
| Syntetical description | FLUSH-MOUNTING SOCKET |
| Protection degree | IP66/IP67 |
| Types of available outlets | STRAIGHT |

Approvals and Certifications



Standards and Laws

-  EN 60309-1 (1999)
[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
-  EN 60309-1/A1 (2007)
[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
-  EN 60309-1/A2 (2012)
[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements

Packaging

Description

Quantity

EAN code

Volume

Dimensions

Box

10

8001636748306

11599.5 CCM

185x285x220 (MM)