

# CabinetMate Plug-In Outlet Center Unit / 120V/20A/48" long/10 O/L /6' cord

4810ULBC20R



Ten 20A outlets with t-slots, 6' [1.8m] cord. Length 48" [1.2m]. Receptacle center-to-center 4" [101mm]. 20 Amp unit with a 20A resettable circuit breaker.

## features & benefits



## specifications

### Technical Information

Amps: 20  
Mounting: 0U  
Rated Voltage: 120V  
Number Of Circuits: 1  
Receptacle Type: NEMA  
Network Monitoring: No  
Surge Suppression: Computer Grade  
Number Of Outlets: 10

### Buy American Act Compliance

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant