

T322, Tantalum, MnO2 Tantalum, Commercial Grade, 22 uF, 10%, 15 VDC, 2 Ohms



| Dimensions |                  |
|------------|------------------|
| D          | 4.57mm MAX       |
| L          | 10.67mm MAX      |
| LL         | 38.1mm +/-6.35mm |
| F          | 0.51mm +/-0.05mm |

| Packaging Specifications |           |
|--------------------------|-----------|
| Packaging:               | Bulk, Bag |
| Packaging Quantity:      | 100       |

| General Information |   |
|---------------------|---|
| Supplier:           | KEMET   |
| Series:             | T322  |
| Dielectric:         | MnO2 Tantalum   |
| Style:              | Axial   |
| Description:        | Axial, Solid Tantalum, Molded, Military (Non-ER), Low ESR |
| Features:           | Low ESR   |
| RoHS:               | Yes   |
| Termination:        | Tin   |
| Lead:               | Wire Leads  |
| Notes:              | Uninsulated   |
| Shelf Life:         | 156 Weeks   |

| Specifications         |   |
|------------------------|---|
| Capacitance:           | 22 uF   |
| Capacitance Tolerance: | 10%   |
| Voltage DC:            | 15 VDC (85C), 10.01 VDC (125C Surge), 0.15 VDC (125C Reverse) |
| Temperature Range:     | -55/+125C   |
| Rated Temperature:     | 85°C  |
| Resistance:            | 2 Ohms (100kHz)   |
| Leakage Current:       | 2.6 uA (25C)  |