


Schnitt A-A / cross section A-A



Zubehör / Accessories :
 Gewindebolzen / threaded bolt
 Gewindehülse / threaded sleeve
 Schichtaufbau im metallisierten Loch für Gewindebolzen siehe Zeichnung 114303
 diameter of drilled hole for threaded bolt see drawing 114303

a : Anschlusslänge beliebig von 3 bis 6 mm; Toleranz ±0.3
 a : terminal length from 3 to 6 mm; tolerance ±0.3

9	30.8	16.8	25.0	8.3	12.5	10.8	5.8	19.3	10.8	0.8		
15	39.1	25.1	33.3	8.3	12.5	10.8	5.8	27.5	10.8	0.8		
25	53.0	38.9	47.0	8.3	12.5	10.8	5.8	41.3	10.8	0.8		
37	69.3	55.3	63.5	8.3	12.5	10.8	5.8	57.7	10.8	0.8		
50	67.0	52.7	61.1	11.0	15.4	10.8	5.8	55.3	13.6	0.9		
Polzahl/ No. of contacts	A	B	C	D	E	F	G	H	J	L		
	±0.3	+0.2	±0.2	+0.2	±0.3	±0.2	+0.3	±0.3	±0.2	±0.1		

Fehlende Masse und Angaben siehe DIN 41652 / Missing information and dimensions according to DIN 41652
 Sonstige Angaben siehe Fertigungsunterlagen / Additional indications please see the production documentation

Information:	Tolerances ISO 2768-m	Scale 2:1
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.	Subject to modification without prior notice. Drawing will not be updated.	Designation TMC-P 9 bis 50-TL-3.0 bis 6.0 TMC-P 9 to 50-TL-3.0 to 6.0
ERNI	Elektroapparate GmbH D-73099 ADELBERG	054960
a	03.02.2000	TMCP
Index	Date	M.00017824.SZN

Ident-Nr / Part No. : 033370
 Polzahl / No. of contacts : 9
 Anschlussart / Terminal Type : TL
 Anschlusslänge / Terminal Length : 6,0
 Bauart / Type : 7
 Anforderungsstufe / Class : 207
 Aufdruck / Logo : ERNI
 Zubehör / Accessory : B#CL-6,3-/HU#4-6,4
 Sonderausführung / Special : CL15