



ENGLISH

## Datasheet

# Black/Yellow 30m PVC Nitrile Blend Air Hose

RS Stock number [197-8500](#)



## Description:

30m Flexible Air Hose.

- A fully flexible rubber/PVC alloy air hose combining the look and feel of rubber without any of the associated negative aspects of rubber
- Excellent abrasion, oil and fuel resistance
- Improved resistance to permanent kink
- Working pressure 20 bar

## Specifications:

Application:	Construction Industry, Oil, Grease Solvents, Air & Water Applications, Workshop Environments for Compressed Air Tools & Spray Guns
Colour:	Black/Yellow
Hose Inside Diameter:	6.3mm
Hose Outside Diameter:	14mm
Length:	30m
Manufacturer Series:	GPA
Material:	PVC Nitrile Blend
Maximum Operating Pressure:	20 bar
Maximum Operating Temperature:	+60°C
Minimum Operating Temperature:	-15°C