

VIP-2/SC/FLK10/LED

Order No.: 2322045

The illustration shows a 14-position version



VARIOFACE module, with screw connection and flat-ribbon cable plug connector, for mounting on NS 32 or NS 35/7.5, with pin strip and short and long locking latches for socket strips, 10-pos., with LED



| Commercial data | |
|--------------------------|--------------------|
| GTIN (EAN) | 4046356450829 |
| sales group | I500 |
| Pack | 1 pcs. |
| Customs tariff | 85369010 |
| Weight/Piece | 0.0916 KG |
| Catalog page information | Page 279 (IF-2009) |

Product notes

WEEE/RoHS-compliant since:
06/03/2009



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

| General data | |
|---|---------|
| Nominal voltage U_N | 24 V DC |
| Max. current carrying capacity per branch | 1 A |
| Number of positions | 10 |
| Width | 34.7 mm |

| | |
|---|------------------|
| Height | 56 mm |
| Depth | 65.5 mm |
| Status display | LED |
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Mounting position | Any |
| Standards/regulations | IEC 60664 |
| | DIN EN 50178 |
| | IEC 62103 |
| Pollution degree | 2 |
| Surge voltage category | II |

Connection data

| | |
|--|--|
| Connection 1 | PCB connection |
| Connection in acc. with standard | IEC / EN |
| Type of connection | Screw connection |
| Conductor cross section solid min. | 0.2 mm ² |
| Conductor cross section solid max. | 4 mm ² |
| Conductor cross section stranded min. | 0.2 mm ² |
| Conductor cross section stranded max. | 2.5 mm ² |
| Conductor cross section AWG/kcmil min. | 24 |
| Conductor cross section AWG/kcmil max | 12 |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Connection 2 | Flat-ribbon cable connection |
| Type of connection | Flat-ribbon cable plug connector in acc. with IEC 60603-13 |
| Number of positions | 10 |

Certificates / Approvals

Certification CUL, UL

CUL

| | |
|-----------------------|-------|
| Nominal voltage U_N | 125 V |
|-----------------------|-------|

| | |
|-----------------------|-------|
| Nominal current I_N | 1 A |
| AWG/kcmil | 30-12 |

UL

| | |
|-----------------------|-------|
| Nominal voltage U_N | 125 V |
| Nominal current I_N | 1 A |
| AWG/kcmil | 30-12 |

Accessories

| Item | Designation | Description |
|------------------------|--------------------------|--|
| Cable/conductor | | |
| 2299204 | FLK 10/EZ-DR/ 50/KONFEK | Round cable set, with two 10-pos. socket strips, (1:1 connection), cable length: 0.5 m |
| 2299217 | FLK 10/EZ-DR/ 100/KONFEK | Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 1 m |
| 2299220 | FLK 10/EZ-DR/ 150/KONFEK | Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 1.5 m |
| 2299233 | FLK 10/EZ-DR/ 200/KONFEK | Round cable set, with two 10-pos. socket strips, (1:1 connection), cable length: 2 m |
| 2299246 | FLK 10/EZ-DR/ 300/KONFEK | Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 3 m |
| 2299259 | FLK 10/EZ-DR/ 400/KONFEK | Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 4 m |
| 2299262 | FLK 10/EZ-DR/ 600/KONFEK | Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 6 m |
| 2299275 | FLK 10/EZ-DR/ 800/KONFEK | Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 8 m |
| 2299288 | FLK 10/EZ-DR/1000/KONFEK | Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 10 m |
| 2295059 | FLK EZ-DR.../.../... | Round cable, with preassembly, not shielded, variable cable length |

Diagrams/Drawings

Circuit diagram

