

> 800/4 Z bits

**Application:**

Slotted screws

Drive:1/4" hexagon, suitable for DIN 3126-F 6.3,
ISO 1173 bit holders**Design:**Tough, ideal for difficult screwdriving jobs
e.g. in sheet steel or metal

Code



mm



mm



mm



"



mm



Code	mm	mm	mm	"	mm	
05059305001	0.5	3.0	50	2"	3.0	10
05059466001	0.5	3.0	70	2 3/4"	3.0	10
05059307001	0.5	4.0	50	2"	4.0	10
05059310001	0.6	3.5	50	2"	3.5	10
05059472001	0.6	3.5	70	2 3/4"	3.5	10
05059450001	0.6	3.5	152	6"	3.5	10
05059315001	0.6	4.5	50	2"	4.5	10
05059489001	0.6	4.5	89	3 1/2"	4.5	10
05059320001	0.8	4.0	50	2"	4.0	10
05059478001	0.8	4.0	70	2 3/4"	4.0	10
05059480001	0.8	4.0	89	3 1/2"	4.0	10
05059451001	0.8	4.0	152	6"	4.0	10
05059325001	0.8	5.5	50	2"	5.5	10
05059330001	1.0	5.5	50	2"	5.5	10
05059486001	1.0	5.5	70	2 3/4"	5.5	10
05059488001	1.0	5.5	89	3 1/2"	5.5	10
05059452001	1.0	5.5	152	6"	5.5	10
05059335001	1.0	6.0	50	2"	6.0	10
05059337001	1.2	6.5	50	2"	6.2	10
05059492001	1.2	6.5	70	2 3/4"	6.2	10
05059490001	1.2	6.5	89	3 1/2"	6.2	10
05059453001	1.2	6.5	152	6"	6.2	10
05059340001	1.2	8.0	50	2"	8.0	10
05059496001	1.2	8.0	89	3 1/2"	8.0	10
05059345001	1.6	8.0	50	2"	8.0	10
05059500001	1.6	8.0	89	3 1/2"	8.0	10