


Crimp contact - CK4,0-ED-4,00BU AG - 1663297

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Turned 4.0 crimp contact, individual female contact, core diameter 4.00 mm², silver-plated



Key commercial data

Packing unit	25 pc
GTIN	 4 017918 123109
Weight per Piece (excluding packing)	2.68 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Electrical characteristics

Note	For HC-M-3 modules
------	--------------------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mechanical characteristics

Conductor cross section	4 mm ²
Connection cross section AWG	12
Stripping length of the individual wire	9.6 mm
Insertion/withdrawal cycles	≥ 500

General

Type	Individual female contact
Series	HC-M-03
Connection method	Crimp connection

Material data

Contact material	Copper alloy
------------------	--------------

Crimp contact - CK4,0-ED-4,00BU AG - 1663297

Technical data

Material data

Contact surface material	Silver-plated
--------------------------	---------------

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000796
ETIM 3.0	EC000796
ETIM 4.0	EC000796
ETIM 5.0	EC000796

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

Approvals

Approvals

Approvals

UL Recognized / GOST

Ex Approvals

Approvals submitted

Approval details

Crimp contact - CK4,0-ED-4,00BU AG - 1663297

Approvals

UL Recognized

GOST

Accessories

Accessories

Assembly tool

Assembly tool - CK4,0-EWZ - 1662735



Contact removal tool, for rotated CK-4,0-... contacts

Crimping tool

Crimping pliers - CRIMPFOX-4,0-ED-6,00 - 1205859



Crimping pliers, for CK 4.0... contacts, for conductor cross sections 3.0 - 6.0 mm²

Drawings

Dimensioned drawing

