



Price* : 51.40 GBP



Main

| | |
|---------------------------|---|
| Range | Spacial |
| Product name | Spacial SBM |
| Device application | Multi-purpose |
| Product or component type | Industrial box |
| Device short name | SBM |
| Enclosure type | Flat face box |
| Enclosure nominal height | 400 mm |
| Enclosure nominal width | 800 mm |
| Enclosure nominal depth | 120 mm |
| Enclosure mounting | Wall mounted |
| Device composition | 6 x cover screw 1 x body 1 x cover |
| Body type | Single piece body folded and welded |
| Type of front cover | Plain door |
| Cover fixing | Half turn metal screw |
| Lock type | Outside sealed area : PZ2 screwdriver captive screw |
| Removable parts | Cover, by captive screws |

Complementary

| | |
|------------------------|-----------------------|
| Material | Sheet steel |
| Surface finish | Polyester powder |
| Colour | Grey (RAL 7035) |
| Standards | IEC 62208 |
| Product certifications | BV DNV GL LR |

UL

| | |
|---------------------------------------|------------------------------|
| IP degree of protection | IP66 IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |
| Ambient air temperature for storage | -35...60 °C |
| Ambient air temperature for operation | -35...80 °C |
| Product weight | 11.88 kg |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1241 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|