

## 1. Model : CL10C200JB8NNNC

## 2. Description

Part no.	CL10C200JB8NNNC
Size (inch / mm)	0603/1608
Thickness (mm)	0.8
Temperature characteristics	C0G
Capacitance	20pF
Capacitance tolerance (%)	± 5 %
Voltage (V)	50

## 3. Frequency characteristics

Network Analyzer, 0.5Vrms, 1MHz to 20GHz

