

# Product information

## 18V IMPACT WRENCH LXT



### DTW251Z

Battery Type	Lithium-ion
Body only machine	1
Voltage	18 v
Impacts	0 - 3200 ipm
Drive Square	½ "
Noise sound pressure	90 dB(A)
Noise sound power	101 dB(A)
Noise K factor	3 dB(A)
No Load Speed	0 - 2100 rpm
Max Torque	230 Nm
Vibration: Fastening Bolt	9 m/sec <sup>2</sup>
Vibration K factor	1.5 m/sec <sup>2</sup>
Net weight	1.7 kg



**STANDARD EQUIPMENT:** 194204-5 18V Li-ion battery

- 1/2
- 22 minute charge time with the air cooled Makstar Optimum Charging System.
- 4 pole motor.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Lithium-ion's 40% weight saving means 18 volt power can be obtained by a battery that weighs the same as a 12 volt Ni-MH battery.
- Conveniently located push button for forward and reverse.
- High comfort grips.
- LED job light with afterglow.

Details correct as of: 18-6-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makita.com](http://www.makita.com)