

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [47745-0100](#)
Status: **Active**
Overview: CMC and CMX Sealed, Hybrid, Modular Connectors
Description: 2.50mm, 3.50mm CMC Header, Right Angle, 28 Position, 1 Port, Black, Peg, Lead-Free

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General

Product Family	PCB Headers
Series	47745
Application	Power, Wire-to-Board
Comments	Coding: Black
Overview	CMC and CMX Sealed, Hybrid, Modular Connectors
Product Name	CMC
UPC	887191161006

Physical

Breakaway	No
Circuits (Loaded)	28
Circuits (maximum)	28
Circuits Detail	5x 2.8mm, 5 x 1.5mm, 18 x 0.635mm terminals
Color - Resin	Black
Durability (mating cycles max)	20
First Mate / Last Break	Yes
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	36.292/g
Number of Rows	4
Orientation	Right Angle
PC Tail Length	2.90mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Carton
Pitch - Mating Interface	2.50mm, 3.50mm, 3.70mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Closed Ends
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Solder or Weld

Electrical

Current - Maximum per Contact	12A, 2.5A, 21A
Voltage - Maximum	14V DC



EU RoHS

ELV and RoHS Compliant

REACH SVHC Contains SVHC: No Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[47745Series](#)

Mates With

.635mm, 1.50mm, 2.80mm, Power CMC Receptacle [64318](#)

Use With

[64318](#) CMC Female, [64322](#) CP 0.6, [64323](#) CP 1.5, [64324](#) CP 2.8, [64320-1301](#) Wire Cap, [64325](#) Blind Plugs

Solder Process Data

Duration at Max. Process Temperature (seconds)	10
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260

Material Info**Reference - Drawing Numbers**

Sales Drawing	SD-47745-100
---------------	--------------

This document was generated on 03/06/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION