

Datasheet

## RS Pro Thermoplastic Knob, M10 x 25

RS Stock No: **702-7746**



### Product Details

RS Pro thermoplastic knob in black colour, features M10 x 25 thread size and matt non-chip finish. It is resistant to most chemicals, UV light and water absorption.

### Features and Benefits

- Matte non-chip finish
- Resistant to most chemicals, UV light and water absorption (1.5% maximum)
- Temperature range: -20 to +110°C (short term withstand +170°C)



ENGLISH

### Specifications:

Body Material	PP
Colour	Black
Insert Material	Stainless Steel
Knob Diameter	60 mm
Knob Shape	4-Arm
Mounting Type	Threaded Stud
Thread Diameter	M10
Thread Length	25 mm
Thread	M10 x 25
Operating Temperature Range	-20 to +110°C
Thread Gender	Male
Finish	Matte