



LOGO! DM8 230R, EXP. MODULE, PU//O: 230V/230V/RELAIS, 2TE, 4 DI/4 DO

Installation type/mounting	
Mounting	on 35 mm DIN rail, 2 spacing units wide
Supply voltage	
Rated value (DC)	
• 115 V DC	Yes
• 230 V DC	Yes
permissible range, lower limit (DC)	100 V
permissible range, upper limit (DC)	253 V
Rated value (AC)	
• 115 V AC	Yes
• 230 V AC	Yes
Digital inputs	
Number of digital inputs	4
Input voltage	
• Type of input voltage	AC/DC
Digital outputs	
Number of digital outputs	4; Relays
short-circuit protection	No
Output current	
• for signal "1" rated value	5 A
Relay outputs	
Switching capacity of contacts	
— with inductive load, max.	3 A
— with resistive load, max.	5 A

EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class B, for use in residential areas	Yes
Degree and class of protection	
Degree of protection to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CSA approval	Yes
UL approval	Yes
FM approval	Yes
Developed in accordance with IEC 61131	Yes
according to VDE 0631	Yes
Marine approval	
• Marine approval	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	55 °C
Dimensions	
Width	36 mm; 2 DU
Height	90 mm
Depth	55 mm
last modified:	20.04.2015