



TECHNICAL CHARACTERISTICS

MATERIAL
 INSULATOR: NYLON 66
 FLAMABILITY RATING: UL94-V0
 COLOR: BEIGE
 PITCH: 2.54MM

ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 UP TO 105°C
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 INSULATOR RESISTANCE: >1000 MOHM
 DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC/MN

STANDARD
 CERTIFIED: E323964

PACKAGING
 BAG

DIMENSION

PINS	A
2	5.60
3	8.10
4	10.70
5	13.20
6	15.80
8	20.90
10	25.90
12	31.00
14	36.10

RoHS Compliant

REV	DATE	FILE	BY
G	12-SEP-14	DIMENSION	AS
F	06-AUG-13	CHARACTERISTIC	QL
E	17-NOV-09	STANDARD	JP
D	30-JAN-06	DRAW	EC
C	30-MAR-04	LEAD FREE	JP
B	19-MAR-04		JP
A	17-JUL-02	PDF	JP

PROJECTION:	
APPROVAL: BB	

GENERAL TOLERANCE
.X = +/- 0.2
.XX = +/- 0.15
UNIT: MM
SCALE:
SHEET: 1/1
DRAW: PEARL

	DESCRIPTION: 2.54 MM FEMALE TERMINAL HOUSING
	WERI PART NO: 6190xx11621

SIZE
A4