

3VU13 CIRCUIT BREAKER SETTING RANGE: 14-20A  
AUX.SWITCH: 1NO+1NC FOR TRANSFORMER LINE SIDE  
PROT.

## Certificates/ approvals:

### General Product Approval



GOST



KETI

### Test Certificates

[Special Test Certificate](#)

### Shipping Approval



LRS

### other

[Confirmation](#)

[Declaration of Conformity](#)

[other](#)

[Environmental Confirmations](#)

## Further information:

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

### Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

### Cax online generator

<http://www.siemens.com/cax>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WWW/view/en/3VU1340-1TN00/all>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VU1340-1TN00](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VU1340-1TN00)

last change: