

Datasheet

RS Pro Insulated Crimp Spade Connector, 0.5mm² to 1.5mm², 22AWG to 16AWG, M3.5 Stud Size, Red Vinyl

RS Stock No: 149-316



Product Details

RS Pro insulated crimp spade connector in red vinyl colour, has 0.5 to 1.5 mm², 22 to 16 AWG wire size and M3.5 stud size. This 14.5 mm connector has a PVC funnel entry range of crimps on reels. It is available in a variety of the most popular sizes.

Features and Benefits

- PVC funnel entry range of crimps on reels
- Available in a variety of the most popular sizes
- Red 0.5 to 1.5 mm², blue 1.5 to 2.5 mm² and yellow 4 to 6 mm²

**Specifications:**

Colour	Red
Contact Material	Copper
Contact Plating	Tin
Insulation	Insulated
Insulation Material	Vinyl
Maximum Wire Size (AWG)	16 AWG
Maximum Wire Size (mm ²)	1.5 mm ²
Minimum Wire Size (AWG)	22 AWG
Minimum Wire Size (mm ²)	0.5 mm ²
Overall Length	19.7 mm
Stud Size	M3.7
Thickness	0.8 mm
Width	6.4 mm
Wire Size	22 to 16 AWG
Current Rating	19 A
Temperature Rating	+75°C
Type	Flared Vinyl without Copper Sleeve
Voltage Rating	600 V