



ENGLISH

Datasheet

Stock No: 291-0072

RS Pro ATEX M20 Brass Cable Gland



Product Details

Cable Glands M20

Brass body
M20 thread
To BS6207 pt2
10 glands per box

Approvals

Certificate: SIRA 02ATEX1305X

Specifications:

Thread Size	M20
Material	Brass
Maximum Cable Diameter	7.9mm
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+450°C
Hazardous Area Certification	ATEX