

Product information

18V 1.3MM LXT METAL SHEAR



BJ5130Z

Battery Type	Lithium-ion
Charging Time	22 min
Body only machine	1
Voltage	18 v
Cutting Capacity	1.3 mm
Max cut in mild steel	1.3 mm
Strokes per Minute	2800 spm
Cutting Capacity Stainless Steel	1.0 mm
Noise sound pressure	74 dB(A)
Noise K factor	3 dB(A)
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Sheet Metal	5.5 m/sec ²
Net weight	2.2 kg



- head rotates through 360 degrees for optimum manoeuvrability
- Head rotates through 360 degrees for optimum manoeuvrability
- 22 minute charge time with the air cooled Makstar Optimum Charging System.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Lithium-ion's 40% weight saving means 18 volt power can be obtained by a battery that weighs the same as a 12 volt Ni-MH battery.

Details correct as of: 17-6-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com