

PLC-BSC- 60DC/21-21

Order No.: 2967316



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2967316>

14 mm PLC basic terminal blocks with screw connection method, input
voltage 60 V DC(without relay or optocoupler)

Commercial data

EAN	4017918164065
Pack	10 pcs.
Customs tariff	85364900
Weight/Piece	0.05617 KG

Product notes

WEEE/RoHS-compliant since:
09/22/2006



<http://www.download.phoenixcontact.com>
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

Input data

Nominal input voltage U_N	60 V DC
Status display	LED

Output data

Compatible components	Miniature relay, REL-MR-60DC/21-21AU, REL-MR-60DC/21-21
-----------------------	---

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Type of connection	Screw connection
Stripping length	8 mm
Screw thread	M3

General data

Length	80 mm
Width	14 mm
Height	94 mm
Color	green
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Operating mode	100% operating factor
Inflammability class acc. to UL 94	V0
Mounting position	Any
Assembly instructions	In rows with zero spacing

Certificates / Approvals



Certification

CUL, CUL Listed, GL, GOST, UL, UL Listed

Address

PHOENIX CONTACT UAB
Svitrigailos Str. 11b
03228 Vilnius, LITHUANIA
Phone +370 5 2106321
Fax +370 5 2106324
<http://www.phoenixcontact.lt>



© 2009 Phoenix Contact
Technical modifications reserved;