

#### 4C9743-1MTR

1 Mtr power lead to free end with Switchcraft 761KS IP rated 2.5mm plug

IP66, IP67, IP68 / NEMA 250 (6P) when mated

- Hollow center pin diameter 2.5mm,
- Locking ring provides security in critical applications
- 20 AWG cable 1 mtr to free end
- Handle/Boot with cable strain relief

Plug Sleeve and Pin: Plated copper alloy

Lock Ring: Plated copper alloy

Lock Ring Thread Size: 7/16-32 UN2B thread

Finger Insulator: Rigid thermoplastic

Insulating Washer: Rigid thermoplastic

Sleeve Terminal: Plated copper alloy, electro-tinned

Handle: Rigid thermoplastic overmolded with thermoplastic elastomer

Handle Thread Size: 5/16-24 UNF 2A

Electrical: Current (carry) 5A at 65°C

#### 4C9743A-2MTR

2 Mtr power lead to free end with Switchcraft 761KS IP rated 2.5mm plug

IP66, IP67, IP68 / NEMA 250 (6P) when mated

- Hollow center pin diameter 2.5mm,
- Locking ring provides security in critical applications
- 20 AWG cable 2MTR to Free end
- Handle/Boot with cable strain relief

Plug Sleeve and Pin: Plated copper alloy

Lock Ring: Plated copper alloy

Lock Ring Thread Size: 7/16-32 UN2B thread

Finger Insulator: Rigid thermoplastic

Insulating Washer: Rigid thermoplastic

Sleeve Terminal: Plated copper alloy, electro-tinned

Handle: Rigid thermoplastic overmolded with thermoplastic elastomer

Handle Thread Size: 5/16-24 UNF 2A

Electrical: Current (carry) 5A at 65°C