STANDARD 16 KEYPAD

APEM

4+4 MATRIX KEYPAD WITH INSERT POCKETS







RoHS COMPLIANT

MECHANICAL SPECIFICATIONS:
CONTACT FORCE 400 grams.
TRAVEL 0.80 TO 0.90 mm.

ELECTRICAL SPECIFICATIONS:
CONTACT VOLTAGE RATING 30V (dc).
CONTACT CURRENT RATING 100mA.
INSULATION RESISTANCE AT 100 V >100 Mohms.
DIELECTRIC STRENGTH 250 V rms.
CAPACITANCE 10 pF typ.
CONTACT BOUNCE BELOW 10 msec. typ.

ENVIRONMENTAL SPECIFICATIONS:
OPERATING TEMPERATURE -30 TO +55 C.
STORAGE TEMPERATURE -40 TO +60 C.



4 INSERTS WITH BLACK GRAPHICS ON A SILVER BACKGROUND
SUPPLIED WITH THIS KEYPAD. FOR OTHER VARIANTS OF INSERTS PLEASE CALL APEM



Telephone: (44) 01844 202400 Fax: (44) 01844 202500 email: sales@apem.co.uk www.apem.co.uk