



ENGLISH

Datasheet

**RS Pro Black PVC Electrical Insulation Tape, 19mm x
33m, 0.15mm Thick
Stock No: 408-9518**



A shiny, self-bonding PVC, reliant on friction and overlap to maintain bond until self-bonding cycle completed.

(Bonding cycle 2 hours at 120°C).

- Easy unwind
- Flexible
- Excellent conformability to awkward shapes
- Water resistant



ENGLISH

Technical Details

Thickness 0.150mm

Breaking Load 21 N/cm

Elongation 250%

Water Extract

pH 6.0 to 8.0

Conductivity Max. 2.5 mS/m

Recommended Self Bonding Temperature 2 hours @ 120°C

B.S. Softness Number (2571) 35 - 45

RoHS Compliant Yes

Service Temperature -18°C to +100°C

Application Temperature 0°C to +40°C

Storage Temperature +12°C to +25°C