

Datasheet

RS Pro Crimp Ring Terminal

RS Stock No: **433-028A**



Product Details

RS Pro crimp ring terminal suits cables from 0.5 mm² to 1.5 mm² and 1.0 mm² to 2.5 mm².

Features and Benefits

- Sheet formed terminal
- Copper contacts
- Accommodates cables of size 0.5 mm² to 1.5 mm² and 1.0 mm² to 2.5 mm²

**Specifications:**

Contact Material	Copper
Contact Plating	Tin
Inner Ring Diameter	3.7 mm
Insulation	Uninsulated
Maximum Wire Size (AWG)	16 AWG
Maximum Wire Size (mm ²)	1.5 mm ²
Minimum Wire Size (AWG)	22 AWG
Minimum Wire Size (mm ²)	0.5 mm ²
Outer Ring Diameter	6.6 mm
Overall Length	19.6 mm
Stud Size	#6
Thickness	0.8 mm
Wire Size	22 to 16 AWG
Temperature Rating	+75°C
Voltage Rating	600 V
Amperage Rating	9 to 18 A
Type	Butted Seam Barrel