

Section Links

A045 | A040 | A095 | A090 | A195 | A190 | A080 | A085 | A087 | A200 | **A070** | A210 | A300 | A315 | A089 | A125 | A105 | A205

Product Details

A070 Mild Steel Plated Base and Stud

Materials Base - Mild Steel, Electroless Nickel Plated
 Stud - Mild Steel, Electroless Nickel Plated



Part No.	Thread Size D1 (mm)	Thread Length L (mm)	Base Diameter D2 (mm)	Overall Height H (mm)	Maximum Recommended Load (kg)
A070/001	M12	75	55	105	1000
A070/002	M12	125	55	155	1000
A070/005	M12	150	55	180	1000
A070/011	M16	75	70	114	1500
A070/018	M16	125	70	164	1500
A070/006	M16	150	70	189	1500
A070/008	M16	200	70	239	1500
A070/020	M20	125	100	177	3000
A070/007	M20	150	100	202	3000
A070/009	M20	200	100	250	3000
A070/028	M24	125	100	181	4000
A070/012	M24	150	100	206	4000
A070/013	M24	200	100	256	4000
A070/029	M24	250	100	306	4000

Dimensions are approximate

