

General Information

Extended Product Type:	FEM4A
Product ID:	1SNA126629R2400
EAN:	3472591266290
Catalog Description:	FEM4A End Sections Blue
Long Description:	FEM4A - End Sections - Blue - 3mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » End Sections

Ordering

EAN:	3472591266290
Minimum Order Quantity:	20 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Weight:	3.8 g
---------------------	-------

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Gross Weight:	0.076 kg
Package Level 1 EAN:	3472591266290
Package Level 2 Units:	800 piece

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
--------------------------	--

Technical UL/CSA

Flammability According to UL94:	V0
---------------------------------	----

Additional Information

Ambient Temperature:	-5 ... +40 °C
Color:	Blue
Function:	End Sections
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Product Main Type:	FEM4A
Product Name:	End Section
Spacing:	3 mm
Suitable For:	M4/6.4A

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225001C1009
RoHS Information:	1SND230478F0202

Classifications

ETIM 4.0:	EC000886 - Endplate and partition plate for terminal block
ETIM 5.0:	EC000886 - Endplate and partition plate for terminal block
Object Classification Code:	X

