


T-1 3/4 MIDGET FLANGE BASE LED



JKL PART NUMBER	EMITTING COLOR	AMPERAGE mA	VOLTAGE Vdc	LUMENS	VIEWING ANGLE
LE-MF-12W	WHITE	15	12	3.5	40°
LE-MF-24W	WHITE	15	24	3.5	40°

OPERATING TEMPERATURE RANGE -30°C TO +85°C

STORAGE TEMPERATURE RANGE -40°C TO +100° C

NOTES:

1. LED includes integrated diode for reverse voltage protection.
2. LED includes integrated resistor for current limiting.

			METRIC  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0	JKL COMPONENTS CORPORATION											
					TITLE											
				T-1 3/4 MIDGET FLANGE BASE LED												
				DRAWN BY		APPV'D BY		DATE		SIZE	FSCM NO.	DRAWING NO.				
				L. WENGSTROM		L.R.		6/13/12		A	55335	LE-MF MULTI				
RELEASED			6/13/12		- CAD DRAWING -		SCALE		RELEASED		REVISION		REV.		SHEET	
REV. NO.			DESCRIPTION/ECO NUMBER		APPV'D DATE		MANUAL REVISIONS NOT PERMITTED		NONE		DATE		DATE		NO.	
											6/13/12				1 OF 1	