



ENGLISH

Datasheet

RS Pro Platform Ladder 4 steps Fibreglass 2.74 to 4.57m open length

RS Stock No: **799-0688**



Product Details

RS Pro platform ladder with 4 steps, is a lightweight professional quality industrial ladder suitable for a range of jobs including multiple sizes of A-frame, 90° ladders, an extension or even as a scaffold system. This little giant horse ladder with fibreglass stiles, has 2.74 to 4.57 m open length and 1.40 m closed length. The multi-purpose ladder meets EN131 standards.

Features and Benefits

- Non conductive fibreglass construction for added protection
- Protective feet to avoid damage to stairs and surfaces and for added stability
- Sturdy flexible hinges and wide legs for further stability
- Glider wheels for easy movement



Specifications:

Closed Length	1.4 m
Ladder Type	Multi-Purpose
Maximum Load	150 kg
Number of Treads	4
Open Length	2.74 to 4.57 m
Stiles Material	Fibreglass
Weight	17.7 kg
Standards Met	EN 131
Step Height	1.32 to 2.18 mm