



## 10769 - OTŞAR111 75W 12V FL GE BX 1/10 MIC

### Specifications

#### General characteristics:

<b>Wattage [W]</b>	75
<b>Voltage [V]</b>	12
<b>Cap/Base</b>	G5.3
<b>Bulb Shape</b>	Reflector
<b>Bulb Diameter [mm]</b>	111
<b>Colour temperature [K]</b>	2900
<b>Colour Rendering Index (CRI) [Ra]</b>	100
<b>Rated Life [h]</b>	3000
<b>Dimming Capability</b>	Yes
<b>Coil type</b>	C-8
<b>Beam Angle [°]</b>	24
<b>Center Beam Candlepower [cd]</b>	5300
<b>Maximum Overall Length [mm]</b>	67
<b>DUN Code</b>	20043168107697
<b>EAN Code</b>	0043168107693
<b>Net weight per piece [g]</b>	50
<b>Gross weight per piece [g]</b>	95
<b>Pack Quantity</b>	10
<b>Layer quantity EUR (PC)</b>	90
<b>Layer quantity UK (PC)</b>	130
<b>Pallet quantity EUR (PC)</b>	630
<b>Pallet quantity UK (PC)</b>	910
<b>Outer case size</b>	444 x 186 x 132 (mm)
<b>Energy Efficiency Class</b>	D
<b>Brand</b>	General Electric (GE)
<b>Product status</b>	Available