




2		1				
LOC	DIST	REVISIONS				
H	—	P	LTR	DESCRIPTION	DATE	APVD
			U	EH-0855-97	04-08-97	J.G
			V	EH-0855-97	04-08-97	J.G
			W	ECR-07-011431	05-06-07	BSV MKO



NOTES


- 1 MATERIAL:
-HOUSING: THERMOPLASTIC POLYESTER, COLOR GREY.
-CONTACTS: BRASS.
- 2 PLATING CONTACT: 1,25 µm Au OVER 1,25 µm Ni IN CONTACT AREA.
Sn over 1,25 µm Ni ON SOLDER POST.
- 3 PLATING CONTACT: 0,8 µm Au OVER 1,25 µm Ni IN CONTACT AREA.
Sn over 1,25 µm Ni ON SOLDER POST.
- 4 PLATING CONTACT: 2,0 µm Au OVER 1,25 µm Ni IN CONTACT AREA.
Sn over 1,25 µm Ni ON SOLDER POST.
- 5 PLATING CONTACT: 0,4 µm Au OVER 1,25 µm Ni IN CONTACT AREA.
Sn over 1,25 µm Ni ON SOLDER POST.
- 6 SOLDER POSTS SUITABLE FOR P.C.B. HOLES
0,8+/-0,05 OR 1,0+/-0,1 DIA.
- 7 8 HOLES SUITABLE FOR KEYING PIN PN. 215916-1.
- 8 KEYING HOLES TO BE DRILLED BY CUSTOMER.



POS. NO	2	4	6	8	10	12	14	16	18	20	22	24	26	28	30	32
F 48 ROW	x	x	x	x	x	x	x	x	x	x	x	x	x	x	x	x

AN ASTERISK „X” DENOTES A STANDARD CONTACT.

2--7 OBSOLETE	SEE NOTE		SEE NOTE 	2-164045-8
	SEE NOTE			2-164045-7
	SEE NOTE			2-164045-4
	SEE NOTE			2-164045-1
		FINISH		MATERIAL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.v.LOKVEN 27AUG91	 Tyco Electronics Corporation 's-Hertogenbosch, Nederland			
DIMENSIONS: mm		CHK J.GIBBELS	NAME 48 POS. DIN 41612 F MALE 90° SOLDER CONNECTOR			
		APVD —				
		PRODUCT SPEC —				
		APPLICATION SPEC —				
MATERIAL —		FINISH —	SIZE A3	CAGE CODE 00779	DRAWING NO C-164045	RESTRICTED TO —
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 2	REV W	

