

Datasheet

RS Pro Stainless Steel IP66 Junction Box, 300 x 120 x 300mm, Natural

RS Stock No: **749-1872**



Product Details

RS Pro junction box in natural colour, is made of stainless steel and measures 300 x 120 x 300 mm. It has IP66 enclosure. This heavy duty terminal box is designed for housing DIN rail terminals and accessories. It is constructed from 1.2 mm AISI 316 natural finish stainless steel and is fitted with a black neoprene gasket.

Features and Benefits

- Lids with black neoprene gasket and 4 x M6 captive hexagon headed screws
- Multiple DIN rail fixing points, M5
- External M6 earthing stud
- Material 316 stainless steel
- IP66 rated
- Operating temperature -20 to +110°C



Specifications:

Colour	Natural
Dimensions (L x W x H)	300 x 120 x 300 mm
Height	300 mm
IP Rating	IP66
Length	300 mm
Material	Stainless Steel
Mounting Type	Wall
Width	120 mm
Wall Thickness	1.2 mm